



POLIMASTER®



Innovating Radiation Detection Technologies Since 1992

SURVEY METER PM1405



The PM1405 Survey Meter measures beta radiation flux density from contaminated surfaces and ambient dose equivalent rate of gamma and X-ray radiation.

Gamma and X-ray radiation dose equivalent measurement and alpha radiation flux density measurement can be optionally provided under customer's request.

The instrument alerts the user with audible alarms when preset radiation thresholds are exceeded and registers with audio signal every detected count in a search mode.

Application-specific user software allows for the remote control of the instruments connected to a PC through USB interface from any PC integrated into the network. This function allows an administrator to monitor and control operation of each instrument.



Applications

- First responders
- Custom and border patrol officers
- Radiological and radionuclide isotope laboratories
- Bank personnel
- Wide range of experts whose activity involves the monitoring of radiation sources

Features

- Dose rate measurement of gamma and X-ray radiation
- Measurement of beta particles flux density
- Search for beta, gamma and X-ray radiation sources mode
- Large LCD display with backlight
- Audible alarm
- Data logging capability
- PC communication via USB
- Universal power supply: two AA batteries or from PC via USB
- Light weight and small dimensions

Optional

- Dose measurement of gamma and X-ray radiation
- Measurement of alpha particles flux density
- Search for alpha radiation sources
- Extended beta flux density measurement range $6.0 - 10^4 \text{ min}^{-1} \cdot \text{cm}^{-2}$



ALARM

LOCATION

MEASUREMENT

USB

www.polimaster.com

www.polimaster.us

www.polimaster.eu

www.polimaster.jp

α
 γ β





SURVEY METER PM1405

SPECIFICATIONS

Gamma detector	Geiger-Mueller counter
Dose equivalent rate (DER) indication range	0.01 $\mu\text{Sv/h}$ - 130 mSv/h
DER measurement range	0.1 $\mu\text{Sv/h}$ - 100 mSv/h
Accuracy of DER measurement	$\pm(20 + K/X)\%$, where X - DER value in $\mu\text{Sv/h}$, K = 1.0 μSv
X-ray and gamma radiation energy range	0.05 to 3.0 MeV
Energy dependence relative to 0.662 MeV (^{137}Cs) in the energy range 0.06 - 3.0 MeV, not more than	$\pm 30\%$
Beta flux density indication range	0.1 - $10^4 \text{ min}^{-1}\cdot\text{cm}^{-2}$
Beta flux density measurement range	6.0 - $10^3 \text{ min}^{-1}\cdot\text{cm}^{-2}$
Accuracy of beta flux density measurement relative to ($^{90}\text{Sr}+^{90}\text{Y}$)	$(20 + A/\varphi)\%$, where φ - beta flux density, $\text{min}^{-1}\cdot\text{cm}^{-2}$, A = 60 $\text{min}^{-1}\cdot\text{cm}^{-2}$
Beta radiation energy range	0.1 to 3.5 MeV
Beta sensitivity relative to ($^{90}\text{Sr}+^{90}\text{Y}$), not less than	3.5 counts$\cdot\text{cm}^2$
Communication with computer	USB interface
Power requirements	two AA batteries or external from PC via USB
Batteries lifetime	6 months typical
Environmental: - temperature range - relative humidity	-10 to +50°C up to 95 % at 35°C
Weight, max	290 g
Dimensions	148x85x40 mm

OPTIONAL SPECIFICATIONS AVAILABLE UNDER REQUEST

Beta flux density measurement range	6.0 - $10^4 \text{ min}^{-1}\cdot\text{cm}^{-2}$
Dose equivalent (DE) indication range	0.01 μSv - 10.0 Sv
DE measurement range	1.0 μSv - 10.0 Sv
Accuracy of DE measurement	$\pm 20\%$
Alpha flux density indication range	0.1 - $10^4 \text{ min}^{-1}\cdot\text{cm}^{-2}$
Alpha flux density measurement range	90 - $10^4 \text{ min}^{-1}\cdot\text{cm}^{-2}$
Accuracy of alpha flux density measurement on ^{239}Pu	$\pm(20 + A/\varphi)\%$, where φ - alpha flux density, $\text{min}^{-1}\cdot\text{cm}^{-2}$, A = 60 $\text{min}^{-1}\cdot\text{cm}^{-2}$

Design and specifications of the device can be changed without further notice.



North and South America Polimaster Inc. 2200 Clarendon Blvd., Ste.1204 Arlington, VA 22201, USA Phone: +1 703 525 5075 Fax: +1 703 525 5079 info@polimaster.us	Europe Polimaster Europe UAB Ezero Str. 4, LT-13264 Didziasalis, Vilnius region, Republic of Lithuania Phone: +370 5 210 2323 Fax: +370 5 210 2322 polimaster@polimaster.lt	Asia, Africa, Australia and Oceania Polimaster Ltd. 112, Bogdanovich St., Minsk, 220040, Republic of Belarus Phone: +375 17 396 3675 +375 17 268 6819 Fax: +375 17 260 2356 polimaster@polimaster.com	Japan Polimaster Pacific K. K. 3rd Floor #32 Arai Building, 3-9-14 Kudan-Minami, Chiyoda-ku Tokyo, Japan Phone: +81 03 6272 4280 Fax: +81 03 6272 4290 pacific@polimaster.jp
---	--	---	--